




Specifications

Coupling : Threaded coupling

Shell material : Zinc alloy with Nickel Plate


Insert material : bakelite

Contact material : copper Silver Plate /Nickel

Termination : Solder

Mating cycle : 500

Cable diameter : -20°C +85°C



Ordering Information

XD - GX20 - NP - *

No. of Pin
2-10 Pin
Contact
Type
F=Female
M=Male

NO. of contacts	芯数	2	3	4	5	6	7	8	9	10	12	14	15
Rated current (A)	额定电流	15A	15A	10A	10A	10A	10A	10A	10A	5A	5A	5A	5A
Operation limit voltage(AC.V.rms) 工作电压(AC.V) 分钟		250V	250V	200V	200V	200V	200V	200V	200V	200V	200V	200V	200V
Withstanding voltage(AC.V.rms) 1 minute 耐压		1500	1500	1500	1000	1000	1000	1000	1000	1000	1000	1000	1000
Insulation resistance (mΩ)	绝缘阻抗	1500	1500	1500	1000	1000	1000	1000	1000	1000	1000	1000	1000
Contact resistance (mΩ)	接触阻抗	3	3	3	3	3	3	3	3	3	3	3	3

			GENERAL TOLERANCE	制图 DRAWING		 深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK					
			X.X ±0.30	批准 APPROVAL		产品名称 TITLE	GX20 航空插头 母头	版本 REV.	A
1	初版发行		X.XX ±0.20	比例 SCALE		产品料号 PART NO.	XD-GX20-NP-F	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX ±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
			Angle ±3.0°						