


Coupling :	Threaded coupling
Shell material:	Brass with Nickel Plate
Insert material:	bakelite
Contact material:	copper Silver Plate/Nickel
Termination:	Solder
Mating cycle:	500
Cable diameter:	-20°C +85°C



7P

No. of Pin 2~7 Pin	Contact Type F=Female M=Male
2 Pin	F
3 Pin	F
4 Pin	F
5 Pin	F
6 Pin	F
7 Pin	F

			GENERAL TOLERANCE	制 图 DRAWING	 深圳讯答科技有限公司 Shenzhen Xunda Technology Co., Ltd			
			DIM TOL	审 核 CHECK				
			X.X ±0.30	批 准 APPROVAL	产品名称 TITLE	GX12 航空插头 公头	版本 REV.	A
1	初版发行		X.XX ±0.20	比 例 SCALE	产品料号 PART NO.	XD-GX12-NP-M	单位 UNITS	mm
			X.XXX ±0.10					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投 影 Projection	 材料 MATERIAL		页次 SHEET	1/1