

公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50

材料及电镀





- ①. 螺 丝: M2.5, 钢, 镀锌, 一字槽
- ②. 塑件主体: PA66, UL94V-0
- ③. 焊 脚: 黄铜, 镀镍
- ④. 方 盒: 黄铜, 镀镍

电气性能

额定电压: 300V
额定电流: 16A
接触电阻: 20mΩ (Max)
绝缘电阻: 500MΩ \DC500V
耐 电 压: AC1600V\1Min
使用线径: 26-14AWG 2.5mm²

机械性能

温度范围: -40℃ ~ +105℃
瞬时温度: +250℃ 5秒
扭 力: 0.4Nm (3.54Lbin)
剥线长度: 4.5-5mm



Ordering Information

HC127 * - * - NP - * - *

Type: 1=直针, 2=弯针
PITCH: 5.00=5mm
No. of Pins: 2-24Pin
2P=2Pin
3P=3Pin
.....
Colour: V=Green, L=Blue, O=Orange, R=Red, B=Black, GR=Gray
Pin: 2=Green, 3=Blue, 4=Orange, 5=Red, 6=Black, 7=Gray
PL=Philips (十字螺丝)
SL=Slotted (一字螺丝)

			GENERAL TOLERANCE	制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审 核 CHECK		产品名称 TITLE	5.00 单排 螺丝式 接线端子 直针 (一字螺丝)	版 本 REV.	A
			X.X ±0.50	批 准 APPROVAL		产品料号 PART NO.	HC127V-5.00-NP-V	单 位 UNITS	mm
1	初版发行		X.XX ±0.30	比 例 SCALE		材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX ±0.10	投 影 Projection					
			Angle ±3.0°						