





	2A	3A	4A	5A	6A	7A	8A	9A	10A	11A	12A	13A	14A	15A	16A
DIM.A	2.50	5.00	7.50	10.00	12.50	15.00	17.50	20.00	22.50	25.00	27.50	30.00	32.50	35.00	37.50
DIM.B	7.5	10.0	12.5	15.0	17.5	20.0	22.5	25.0	27.5	30.0	32.5	35.0	37.5	40.0	42.5

					TOLERANCE UNLESS SPECIFIED								
					UP TO 5mm:±0.1	ANGLES							
					ABOVE 5mm:±0.2	±1.5°	NO	DATE	REVISIONS			BY	APPD
					TITLE: XH 2.5mm connector				UNIT : MM	ROHS	DWN		
					PART NO.: XHS2500-03R				SCALE: 2:1	COMPLIANT	CHK'D		
2	CONTACT	BRASS	XX	SN-PLATED	 HAOYU(HONG KONG)LIMITED 皓宇(香港)有限公司					APPD			
1	PEDESTAL	PA66(UL94V-0)	1	WHITE									
NO.	PART NAME	MATERIAL	QTY	FINISHING						PRO.AGL: 		REV :A0	