





SCHEMATIC

P. C. B LAYOUT
TOP VIEW

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 50MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	180±50gf
行程 Travels	0.2±0.1mm

					TOLERANCE							
					UNLESS SPECIFIED							
					UP TO 5mm:±0.1	ANGULAR	1					
5	COVER	PBS	1	Ag-PLATED	ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
4	CONTACT FOOT	PBS	2	Ag-PLATED	TITLE: TACT SWITCH			UNIT : MM		ROHS	DWN	
3	COAT	SUS	1	Ag-CLAD	MODEL: TS-1114A-C			SCALE: 1:1		COMPLIANT	CHK'D	
2	BUTTON	LCP	1		 HAOYU(HONGKONG)LIMITED 皓 宇(香 港)有 限 公 司					APPD		
1	HOUSING	LCP	1							PRO.AGL: 		REV :A0
NO.	PART NAME	MATERIAL	QTY	FINISHING								