








P.C.B LAYOUT



SCHEMATIC

H=6.5 mm



SPECIFICATION

- 1.Rating : DC12V 50mA.
 - 2.Contact resistance: $\leq 100\text{m}\Omega$.
 - 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
 - 4.Withstanding voltage: 250VAC .
 - 5.Operating Force: $200 \pm 100\text{gf}$.
 - 6.Travel: $0.25 \pm 0.1\text{mm}$.
 - 7.life test: 100,000 cycles.
 - 8.Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
 - 9.Sign"* "is importance dimension.
- TEL: 0769-82310510-867

脚距 L

8.0 mm

8.8 mm

9.8 mm

					TOLERANCE								
					UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°							
5	KNOB	PA9T	1	BLACK/RED			NO	DATE	REVISIONS			BY	APPD
4	COVER	BRASS/SUS	1	Sn-PLating	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
3	CONTACT	SUS	1	Ag-Plated	MODEL: TC-06104-065E-01				SCALE: 1:1	COMPLIANT	CHK'D		
2	CASE	PA9T	1	BLACK	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD		PRO.AGL: 		REV :A0
1	TERMINAL	BRASS	1	Ag-Plated									
NO.	PART NAME	MATERIAL	QTY	FINISHING									