






SPECIFICATION

1. Rating: DC 6V 0.3A
 2. Travel: 2 mm
 3. Function: 2P5T
 4. Contact Resistance: $\leq 70\text{m}\Omega\text{MAX}$
 5. Operating Force: $250\pm 80\text{gf}$
 6. Life test: 10,000 cycles
- KNOB G= 2.0, 3.0, 4.0 5.0mm



SCHEMATIC



P.C.B LAYOUT

				TOLERANCE UNLESS SPECIFIED							
				UP TO 5mm: ± 0.1	ANGULAR						
				ABOVE 5mm: ± 0.2	$\pm 1^\circ$	NO	DATE	REVISIONS		BY	APPD
4	MK22D10A	Phosphor copper	2	NATURAL	TITLE: MINI SLIDE SWITCH		UNIT : MM	ROHS	DWN		
3	MS25D20 KNOB	PA46	1	BLACK	MODEL: MS-25D20G5.5-B		SCALE: 6:1	COMPLIANT	CHK'D		
2	MS25D20 COVER	SUS301	1	WASHING	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司				APPD		
1	MS25D20 CASE	LCP/ BRASS	1	BLACK/Au/Ag PLATED							
NO.	PART	NAME	MATERIAL	QTY	FINISHING					PRO.AGL:	REV :A0