




SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $160\pm 50gf/250\pm 80gf$
- 6.Travel: $0.25\pm 0.1mm$.
- 7.life test: 10,000 cycles.
- 8.Operation temperature range: $-25^{\circ}C\sim 85^{\circ}C$.
- 9.Sign"* "is importance dimension.



CIRCUIT DIAGRAM



P . C . B LAYOUT

				TOLERANCE UNLESS SPECIFIED							
				<1.5: $\pm 0.1mm$	ANGULAR $\pm 1^{\circ}$	A1	2023.2.17	更新图纸		WM	
				>1.5~5.0: $\pm 0.25mm$		NO	DATE	REVISIONS		BY	APPD
				>5.0: $\pm 0.3mm$							
1	TERMINAL	BRASS	1	Ag-PLATED	TITLE: TACT SWITCH		UNIT : MM	ROHS	DWN		
2	CASE	PA9T	1	BLACK	MODEL: TC-00104-045E-01		SCALE: 1:1	COMPLIANT	CHK'D		
3	CONTACT	SUS301	1	Ag-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD		
4	COVER	BRASS	1	Sn-PLATED							
5	KNOB	PA9T	1	BLACK							
NO.	PART	NAME	MATERIAL	QTY	FINISHING			PRO.AGL: 		REV :A1	