



**SPECIFICATION**

- 1.Rating : DC12V 50mA.
  - 2.Contact resistance:  $\leq 100m\Omega$ .
  - 3.Insulation resistance:  $\geq 100M\Omega$  (DC100V).
  - 4.Withstanding voltage: 250VAC .
  - 5.Operating Force:  $160\pm 50gf/250\pm 80gf$
  - 6.Travel: $0.2\pm 0.1mm$ .
  - 7.life test: 10,000 cycles.
  - 8.Operation temperature range:  $-25^{\circ}C\sim 85^{\circ}C$ .
  - 9.Sign "\*" is importance dimension.
- TEL:0769-82310510-867



CIRCUIT DIAGRAM



				TOLERANCE UNLESS SPECIFIED									
				<1.5: $\pm 0.1mm$	ANGULAR $\pm 1^{\circ}$	NO	DATE	REVISIONS		BY	APPD		
				>1.5~5.0: $\pm 0.25mm$								DWN	
				>5.0: $\pm 0.3mm$								CHK'D	
5	KNOB	PA9T	1		TITLE: TACT SWITCH		UNIT : MM	ROHS COMPLIANT	DWN				
4	COVER	BRASS	1	SN-PLATED	MODEL: TC-06204-043E		SCALE: 1:1		CHK'D				
3	CONTACT	SUS	1	AG-PLATED	DONGGUANG HAOYU ELECTRONICS CO., LTD				APPD				
2	CASE	PA9T	1		皓宇 HOOYA 东莞市弘皓电子有限公司				APPD				
1	TERMINAL	BRASS	1	AG-PLATED					APPD				
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL:		REV :AO		