






SPECIFICATION

- 1.Rating : DC12V 50mA.
 - 2.Contact resistance: $\leq 100m\Omega$.
 - 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
 - 4.Withstanding voltage: 250VAC .
 - 5.Operating Force: $250\pm 80gf$
 - 6.Travel: $0.2\pm 0.1mm$.
 - 7.life test: 10,000 cycles.
 - 8.Operation temperature range: $-25^{\circ}C\sim 85^{\circ}C$.
 - 9.Sign"* "is importance dimension.
- TEL:0769-82310510-867



CIRCUIT DIAGRAM



P . C . B LAYOUT

H=3.8mm
H=4.0mm
H=4.3mm
H=4.5mm
H=5.0mm
H=5.5mm
H=6.0mm
H=6.5mm
H=7.0mm
H=8.0mm
H=9.0mm

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°							
5	KNOB	PA9T	1				NO	DATE	REVISIONS			BY	APPD
4	COVER	BRASS	1	SN-PLATED	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
3	CONTACT	SUS	1	AG-PLATED	MODEL: TC-06204-065E-01				SCALE: 1:1	COMPLIANT	CHK'D		
2	CASE	PA9T	1		 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD				
1	TERMINAL	BRASS	1	AG-PLATED									
NO.	PART	NAME	MATERIAL	QTY	FINISHING				PRO.AGL: 				REV :A0