




	2A	3A	4A	5A	6A	7A	8A	9A	10A	11A	12A	13A	14A	15A	16A
DIM.A	2.50	5.00	7.50	10.00	12.50	15.00	17.50	20.00	22.50	25.00	27.50	30.00	32.50	35.00	37.50
DIM.B	7.5	10.0	12.5	15.0	17.5	20.0	22.5	25.0	27.5	30.0	32.5	35.0	37.5	40.0	42.5

					TOLERANCE UNLESS SPECIFIED										
					UP TO 5mm: ± 0.1	ANGLES									
					ABOVE 5mm: ± 0.2	$\pm 1.5^\circ$	NO	DATE	REVISIONS				BY	APPD	
					TITLE: XH 2.5mm connector					UNIT : MM	ROHS	DWN			
					PART NO.: XHS2500-02R					SCALE: 2:1	COMPLIANT	CHK'D			
2	CONTACT	BRASS	XX	SN-PLATED											
1	PEDESTAL	PA66(UL94V-0)	1	WHITE											
NO.	PART	NAME	MATERIAL	QTY	FINISHING										
					 HAOYU(HONG KONG)LIMITED 皓宇(香港)有限公司							PRO.AGL:	 	REV :A0	