



材料Material

胶芯原料Insulator:PA46,(UL 94V-0)

外壳材料Related Material: Brass

表面涂层Surface Coating:Nickel Plating

针材料Related Material: Male-Brass

Female-Bronze

表面涂层Surface Coating:Overgold 1u

规格参数Planning Parameters

绝缘电阻Insulation Resistance: $\geq 100M\Omega$

工作温度Operating Temperature: $-40+150^{\circ}$

M12-A-XP-M-BQ3-HX

- HX-面板杯口焊线式
- HB-面板PCB焊板式
- BQ1-面板前锁
- BQ3-面板长螺纹前锁
- BH1-面板后锁
- M-公端 F-母端
- XP-4P 5P 8P 12P
- A-编码

上海洲日电子有限公司

Shanghai Zhouri Electronics CO.,LTD

上海康司玛电子设备进出口有限公司

Shanghai Zhouri Electronics Import And Export Co.,LTD

tel:021-51571121
fax:021-51571120

<http://www.zhourri.net>

产品名称:

M12-A-XP-M-BQ3-HX

绘图:	MAXIA	日期: 20211027
审核:	张海娜	日期: 20211027
版本编号:	ZRLCGY2021-10-20-CJ/2	
第三视角:		单位: mm

芯数 Pin	额定电流 Rate Current	额定电压 Rate Voltage	耐压 Dielectric Withstanding Voltage
4	4A	250V	1500 V/Min
5	4A	250V	1200 V/Min
8	2A	30V	500 V/Min
12	1A	30V	500 V/Min