








P.C.B LAYOUT



SCHEMATIC

H=9.0 mm



## SPECIFICATION

- 1.Rating : DC12V 50mA.
  - 2.Contact resistance:  $\leq 100\text{m}\Omega$ .
  - 3.Insulation resistance:  $\geq 100\text{M}\Omega$  (DC100V).
  - 4.Withstanding voltage: 250VAC .
  - 5.Operating Force:  $200\pm 100\text{gf}$ .
  - 6.Travel: $0.25\pm 0.1\text{mm}$ .
  - 7.life test: 100,000 cycles.
  - 8.Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$ .
  - 9.Sign"\* "is importance dimension.
- TEL: 0769-82310510-867

脚距 L

8.0 mm

8.8 mm

9.8 mm

|     |           |           |     |            |                                                                                                                                           |                |    |      |            |                                                                                                                                                                                              |       |    |      |
|-----|-----------|-----------|-----|------------|-------------------------------------------------------------------------------------------------------------------------------------------|----------------|----|------|------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|----|------|
|     |           |           |     |            | TOLERANCE<br>UNLESS SPECIFIED                                                                                                             |                |    |      |            |                                                                                                                                                                                              |       |    |      |
|     |           |           |     |            |                                                                                                                                           |                |    |      |            |                                                                                                                                                                                              |       |    |      |
|     |           |           |     |            | <1.5: ±0.1mm<br>>1.5~5.0: ±0.25mm<br>>5.0: ±0.3mm                                                                                         | ANGULAR<br>±1° |    |      |            |                                                                                                                                                                                              |       |    |      |
| 5   | KNOB      | PA9T      | 1   | BLACK/RED  |                                                                                                                                           |                | NO | DATE | REVISIONS  |                                                                                                                                                                                              |       | BY | APPD |
| 4   | COVER     | BRASS/SUS | 1   | Sn-PLating | TITLE: TACT SWITCH                                                                                                                        |                |    |      | UNIT : MM  | ROHS                                                                                                                                                                                         | DWN   |    |      |
| 3   | CONTACT   | SUS       | 1   | Ag-Plated  | MODEL: TC-06104-090E-01                                                                                                                   |                |    |      | SCALE: 1:1 | COMPLIANT                                                                                                                                                                                    | CHK'D |    |      |
| 2   | CASE      | PA9T      | 1   | BLACK      |  DONGGUANG HAOYU ELECTRONICS CO., LTD<br>东莞市弘皓电子有限公司 |                |    |      | APPD       | PRO.AGL:   REV :A0 |       |    |      |
| 1   | TERMINAL  | BRASS     | 1   | Ag-Plated  |                                                                                                                                           |                |    |      |            |                                                                                                                                                                                              |       |    |      |
| NO. | PART NAME | MATERIAL  | QTY | FINISHING  |                                                                                                                                           |                |    |      |            |                                                                                                                                                                                              |       |    |      |