








SCHEMATIC



P.C.B LAYOUT

SPECIFICATION

1. Rating: DC 6V 0.3A
 2. Travel: 2 mm
 3. Function: 2P5T
 4. Contact Resistance: $\leq 70m\Omega$ MAX
 5. Operating Force: $250\pm 80gf$
 6. Life test: 10,000 cycles
- KNOB G= 2.0, 3.0, 4.0 5.0mm

					TOLERANCE UNLESS SPECIFIED								
					UP TO 5mm: ±0.1	ANGULAR							
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS			BY	APPD
4	MK22D10A	Phosphor copper	2	NATURAL	TITLE:MINI SLIDE SWITCH				UNIT : MM	ROHS	DWN		
3	MK25D20 KNOB	PA46	1	BLACK	MODEL: MK-25D18G4-B				SCALE: 6:1	COMPLIANT	CHK'D		
2	MK25D20 COVER	SUS301	1	WASHING	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司						APPD		
1	MS25D18 CASE	LCP/ BRASS	1	BLACK/Au/Ag PLATED									
NO.	PART	NAME	MATERIAL	QTY	FINISHING				PRO.AGL: 			REV :A3	