






SPECIFICATION

- 1.Rating :DC12V 50mA.
 - 2.Contact resistance: $\leq 100m\Omega$.
 - 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
 - 4.Withstanding voltage: 250VAC .
 - 5.Operating Force: $160\pm 50gf/250\pm 80gf$
 - 6.Travel: $0.2\pm 0.1mm$.
 - 7.life test: 10,000 cycles.
 - 8.Operation temperature range: $-25^{\circ}C\sim 85^{\circ}C$.
 - 9.Sign "*" is importance dimension.
- TEL:0769-82310510-867



CIRCUIT DIAGRAM



P . C . B LAYOUT

				TOLERANCE UNLESS SPECIFIED							
				<1.5: $\pm 0.1mm$ >1.5~5.0: $\pm 0.25mm$ >5.0: $\pm 0.3mm$	ANGULAR $\pm 1^{\circ}$						
5	KNOB	PA9T	1			NO	DATE	REVISIONS		BY	APPD
4	COVER	BRASS	1	SN-PLATED	TITLE: TACT SWITCH		UNIT : MM	ROHS COMPLIANT	DWN		
3	CONTACT	SUS	1	AG-PLATED	MODEL: TC-06204-038E-01		SCALE: 1:1		CHK'D		
2	CASE	PA9T	1		 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD		
1	TERMINAL	BRASS	1	AG-PLATED							
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL:	 	REV :A0