




P.C.B LAND DIMENSION



CIRCUIT DIAGRAM



REFERENCE DRAWING



Travel: 0.2±0.1mm

SPECIFICATION

1. Rating : DC12V 50mA.
2. Contact resistance: $\leq 100m\Omega$.
3. Insulation resistance: $\geq 100M\Omega$ (DC100V).
4. Withstanding voltage: 250VAC .
5. Operating Force: $250\pm 80gf$
6. life test: 10,000 cycles.
7. Operation temperature range: $-25^{\circ}C\sim 85^{\circ}C$.
8. Sign"* "is importance dimension.

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		A2	2022.12.28	更新材质表	WM
					UP TO 5mm: ±0.1	ANGULAR ±1°				
5	STEM	LCP/RUBBER	1	WHITE/BLUE	ABOVE 5mm: ±0.2		NO	DATE	REVISIONS	BY APPD
4	COVER	BRASS	1							
3	CONTACT	SUS	4	Ag-PLATED						
2	TERMINAL	PHOSPHOR BRONZE	1	Ag-PLATED						
1	BASE	LCP	1	WHITE						
					TITLE: TACT SWITCH			UNIT : MM	ROHS COMPLIANT	DWN
					MODEL: TS-1188U-E			SCALE: 1:1		CHK'D
					DONGGUANG HAOYU ELECTRONICS CO., LTD			APPD		
					皓宇 HAOYU 东莞市弘皓电子有限公司			PRO.AGL:		REV :A2