






SPECIFICATION

- 1.Rating : DC12V 50mA.
 - 2.Contact resistance: $\leq 100m\Omega$.
 - 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
 - 4.Withstanding voltage: 250VAC .
 - 5.Operating Force: $250\pm 80gf$
 - 6.Travel: $0.2\pm 0.1mm$.
 - 7.life test: 10,000 cycles.
 - 8.Operation temperature range: $-25^{\circ}C\sim 85^{\circ}C$.
 - 9.Sign "*" is importance dimension.
- TEL:0769-82310510-867



CIRCUIT DIAGRAM



P . C . B LAYOUT

				TOLERANCE UNLESS SPECIFIED							
				<1.5: $\pm 0.1mm$	ANGULAR $\pm 1^{\circ}$						
				>1.5~5.0: $\pm 0.25mm$							
				>5.0: $\pm 0.3mm$		NO	DATE	REVISIONS		BY	APPD
5	KNOB	PA9T	1			TITLE: TACT SWITCH		UNIT : MM	ROHS COMPLIANT	DWN	
4	COVER	BRASS	1	SN-PLATED		MODEL: TC-06204-055E-01		SCALE: 1:1		CHK'D	
3	CONTACT	SUS	1	AG-PLATED		 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD	
2	CASE	PA9T	1								
1	TERMINAL	BRASS	1	AG-PLATED							
NO.	PART	NAME	MATERIAL	QTY	FINISHING			PRO.AGL: 		REV :A0	