

Specification Sheet

Part Number: 156-01429



Design gives quick and easy assembly by hand without the need for tools. Mount can be used in a wide variety of applications where 8mm weld studs or 8mm ISO bolts.

Design provides low insertion force and high extraction force.

2-Piece M8 Stud Mount Tie, 8.0" Tie, 50lb Tensile Strength, PA66HS/PA66HIRHSUV, Black, 2000/pkg

Article Number 156-01429

Type T50RSB8SET

Color Black (BK)

Quantity Per bag

Product Description Unique, two-piece design allows routing to be above, parallel or perpendicular to stud. This also enables up to three separate bundles to be fastened to the same stud. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description 2-Piece M8 Stud Mount Tie, 8.0" Tie, 50lb Tensile Strength, PA66HS/PA66HIRHSUV, Black, 2000/pkg

Global Part Name T50RSB8SET-PA66HS/PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 225

Length L (Imperial) 7.95

Length L (Metric) 202.0

Fixation Method Stud Mount

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Width W (Imperial) 0.181

Width W (Metric) 4.6

Bundle Diameter Min (Imperial) 0.16

Bundle Diameter Min (Metric) 4.0

Bundle Diameter Max (Imperial) 1.97

Bundle Diameter Max (Metric) 50.0

Thickness T (Metric) 1.2

Height H (Imperial)	0.98
Height H (Metric)	25.0
Stud Diameter (Metric)	8.0 mm
Stud Diameter (Imperial)	0.31
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +257°F (-40°C to +125°C) -40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)