

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A		NEW		22.3.4

NOTES1:

UL Standard

1.Rated voltage/current : 150V / 8A

2.Withstanding voltage : AC1250V/1Min.

IEC Standard

- | | |
|--------------------------|-------|
| Pollution degree | 2 |
| Overvoltage category | III |
| Rate impulse voltage(KV) | 2.5KV |
| Rate voltage(V) | 320V |
| Rate current(A) | 10A |

NOTES2:

1.Dimension shall be interpreted per ASME Y14.5-2009

2.Pitch : 2.54mm, Poles : N=04~48P

3.Operating temperature: -40℃~+105℃

4.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm							
	Over 6 TO 6	Over 10 TO 10	Over 10 TO 24	Over 30 TO 30	Over 60 TO 60	Over 100 TO 100	Over 150 TO 150	0.1/10	
	±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°

5.RoHS Compliance

Ordering Information

JL15EDGVHDM-254

XX

B

0



1

Pitch 254=2.54PH

No.of pins 4P~48P

Housing Color B=Black G=Green U=Blue R=Red W=White Y=Yellow O=Orange E=Grey

Packing 0=Pe bag T=Tube A=Tray



PCB LAYOUT

DRAW	SHUANGPING ZHENG	SCALE	FIT	JILN® 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
		UNIT	mm		
CHECK	LICHAO LIU	SIZE	A4	PART NO.	JL15EDGVHDM-254XXB01
APPROVE	YONGLIANG GAO	SHEET	1/1	TITLE:	JL15EDGVHDM-THR-2.54-2XNP
		PROJ.			插拔式公座/带耳/直针/黑色