


Specification Sheet

Part Number: 133-01476



U-Shape channel provides 3 sides of protection.

Flattens round bundles to fit through space constrained areas.

Polypropylene material provides good chemical and heat resistance.

Mini-Channel, 1.97" Long, U-Shape, PPT20, Black, 3000/pkg

Article Number	133-01476
----------------	-----------

Type	MINICHNLU
------	-----------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	HellermannTyton Mini Channels provide protection and configurable routing in a cost-effective wire management solution. The variety of sizes and configurations enables engineers and installers to create optimum routing scenarios. Mini channels replace engineered channels that are costly to design and develop.
---------------------	--

Short Description	Mini-Channel, 1.97" Long, U-Shape, PPT20, Black, 3000/pkg
-------------------	---

Global Part Name	MINICHNLU-PPTD20-BK
------------------	---------------------

Length L (Imperial) 1.97

Length L (Metric) 50.0

Width W (Imperial) 0.31

Width W (Metric) 8.0

Height H (Imperial) 1.18

Height H (Metric) 30.0

Material Polypropylene 20% Talkum (PPTD20)

Material Shortcut PPTD20

Flammability UL 94 HB

UV Resistant (Yes/No) No

Operating Temperature -40°F to +149°F (-40°C to +65°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 3000

Package Quantity (Metric)	3000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).