






CAD GENERATED DRAWING. DON' T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB. WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max. initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.15±0.1mm
Storage Temperature	- 30° C to 80° C


C	DOVE	Stainless Steel	1	Plated Ag
B	HOUSING	LCP	1	Black
A	Cards	Phosphor copper	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

Mechanical

P/N	Operating Force(gf)	Height mm	Button	Leads Shape (G, J, L)	Ground pin (0, 1)	Pins Option (0, 1)
BTSOC002	2	250±50			0 (None)	0 (None)
	1	180±50	A	0.65		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Bozhong TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED.

X. ±0.50	X. ° ±2°	UNITS mm
.X ±0.30	.X° ±1°	
.XX ±0.10	.XX° ±0.5°	MAT'L
.XXX ±0.05		
FINISH		
Q' TY		

 博众电气 东莞市博众电气有限公司 Dongguan Bozhong Electrical Co., Ltd	PART NO. BTSOC002	TITLE: TACTILE SWITCH 4.8x4.8x0.55
APPD: ROGER	CHKD: ROC	DWG NO.: BTSOC002
DR: BILLY WANG 2020/08/21		
	SCALE 1/1	SHEET 1/1
	REV. A1	