







RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB. WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max.initial
Dielectric Strength	250 V AC(1mn)
Travel	0.25±0.15mm
Storage Temperature	-30° C to 80° C

Mechanical

E	Button	LCP	1	Black
D	COVER	Stainless Steel	1	Cleaning
C	DOVE	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	PIN	PHOSPHOR BRONZE	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

Type	Operating Force(gf)	Height mm	Button	Leads Shape(G, J, T)	Ground pin 0 (0.1)	Pegs Option 0 (0.1)
BTS0A007	3	320±50	E	2.5	1 (Ground pin) 0 (0.1)	0 (None)
	2	250±50	D	2.0		
			C	1.8		
	1	160±50	B	1.7		
			A	1.5		

X.	±0.50	X.°	±2°
.X	±0.30	.X°	±1°
.XX	±0.10	.XX°	±0.5°
.XXX	±0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF BoZhong TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED.

UNITS	mm
MAT'L	
FINISH	
Q'TY	

 博众电气	东莞市博众电气有限公司
Bozhong Electric	Dongguan Bozhong Electrical Co., Ltd
PART NO.	BTS0A007
APPD:	ROGER
CHKD:	ROC
DR:	BILLY WANG 2020/08/21

Packaging:
Reel of 4,000 pieces.

TITLE:	TACTILE SWITCH 3x3
DWG NO.:	BTS0A007
SCALE	1/1
SHEET	1/1
REV.	A1