





SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°C to +105°C
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

Part No	Pin	A	B	Part No	Pin	A	B	Part No	Pin	A	B	Part No	Pin	A	B
PZ2.54-UP1D-1A	1	0.00	2.54	PZ2.54-UP1D-11A	11	25.40	27.94	PZ2.54-UP1D-21A	21	50.80	53.34	PZ2.54-UP1D-31A	31	76.20	78.74
PZ2.54-UP1D-2A	2	2.54	5.08	PZ2.54-UP1D-12A	12	27.94	30.48	PZ2.54-UP1D-22A	22	53.34	55.88	PZ2.54-UP1D-32A	32	78.74	81.28
PZ2.54-UP1D-3A	3	5.08	7.62	PZ2.54-UP1D-13A	13	30.48	33.02	PZ2.54-UP1D-23A	23	55.88	58.42	PZ2.54-UP1D-33A	33	81.28	83.82
PZ2.54-UP1D-4A	4	7.62	10.16	PZ2.54-UP1D-14A	14	33.02	35.56	PZ2.54-UP1D-24A	24	58.42	60.96	PZ2.54-UP1D-34A	34	83.82	86.36
PZ2.54-UP1D-5A	5	10.16	12.70	PZ2.54-UP1D-15A	15	35.56	38.10	PZ2.54-UP1D-25A	25	60.96	63.50	PZ2.54-UP1D-35A	35	86.36	88.90
PZ2.54-UP1D-6A	6	12.70	15.24	PZ2.54-UP1D-16A	16	38.10	40.64	PZ2.54-UP1D-26A	26	63.50	66.04	PZ2.54-UP1D-36A	36	88.90	91.44
PZ2.54-UP1D-7A	7	15.24	17.78	PZ2.54-UP1D-17A	17	40.64	43.18	PZ2.54-UP1D-27A	27	66.04	68.58	PZ2.54-UP1D-37A	37	91.44	93.95
PZ2.54-UP1D-8A	8	17.78	20.32	PZ2.54-UP1D-18A	18	43.18	45.72	PZ2.54-UP1D-28A	28	68.58	71.12	PZ2.54-UP1D-38A	38	93.95	96.52
PZ2.54-UP1D-9A	9	20.32	22.86	PZ2.54-UP1D-19A	19	45.72	48.26	PZ2.54-UP1D-29A	29	71.12	73.66	PZ2.54-UP1D-39A	39	96.52	99.06
PZ2.54-UP1D-10A	10	25.40	25.40	PZ2.54-UP1D-20A	20	48.26	50.80	PZ2.54-UP1D-30A	30	73.66	76.20	PZ2.54-UP1D-40A	40	99.06	101.60

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.35	.X°± 5°	APR. Alex	TITLE: 2.54PZ H2.5 1xnPin 180° PC3.0 PA6.0 PB2.5 L11.5 6T			
.XX±0.25	.X°± 3°	CHK. Jack	DWG NO. PZ2.54-UP1D-NA			
.XXX±0.15	.XX°± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A