





PC Board Layout
Component Side Shown

NOTES:

MATERIAL:

1. HOUSING MATERIAL :PA46 UL94V-0.
2. CONTACT MATERIAL :PHOSPHOR BRONZE
 $\phi=0,46\text{mm}$.
3. PLATING : 1" GOLD OVER NICKEL
- 4.SHIELD: :0,20mmTHICKNESS COPPER ALLY
WITH NICKEL PLATED

ELECTRICAL:

1. VOLTAGE RATING :125 VAC RMS.
2. CURRENT RATING :1.5 AMP.
3. CONTACT RESISTANCE :30 MILIOHNS MAX.
4. INSULATION RESISTANCE :500 MEGOHMS
MIN @ 500V DC .
5. DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS

50Hz. 1MIN.

MECHANICAL:

1. DURRABILITY :750 CYCLES MIN.
2. PCB RETENTION PRE-SOLDER :1 LB MIN .

ENVIRONMENTAL:

1. STORAGE: -40°C TO 85°C.
2. OPERATION: -25°C TO 80°C.

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD							
CHECKED:	DATE:	TITLE: RJ45-8P/8C 直插 带屏蔽 无灯 无弹片(脚前3.05) PA46料							
DRAWN: SXA	DATE: 2019-07-23	PART. NO.		R-RJ45S08P-BT00					
		UNIT	mm	SCALE	free				
		FILE NO.	Ckmtw-RJ45-0305		REV.	A	RH00		