





RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB. WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max. initial
Dielectric Strength	250 V AC(1mm)
Travel	0.2±0.15mm
Storage Temperature	-30° C to 80° C

ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR
E	Button	LCP/Silica	1	Black/Blue
D	COVER	Stainless Steel	1	Cleaning
C	DOME	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	PIN	PHOSPHOR BRONZE	1	Plated Ag

Mechanical

Type	Operating Force(gf)		Height mm		Button	Leads Shape (G, J, T)	Ground pin (0, 1)	Pogo Option (0, 1)
BTS0A008			C	2.5	U(Blue) B(Black)	G	0 (None)	0 (None)
	2	250±50	B	2.0				
	1	180±50	A	1.8				

X.	± 0.50	X. °	± 2°
.X	± 0.30	.X °	± 1°
.XX	± 0.10	.XX °	± 0.5°
.XXX	± 0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Bozhong TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED.

UNITS	mm
MAT'L	
FINISH	
Q'TY	

	东莞市博众电气有限公司 Dongguan Bozhong Electrical Co., Ltd
PART NO. BTS0A008	TITLE: TACTILE SWITCH 3x3.5mm
APPD: ROGER	DWG NO.: BTS0A008
CHKD: ROC	
DR: BILLY WANG 2020/08/21	

Packaging:
Reel of 4,000 pieces.

SCALE	SHEET	REV.
1/1	1/1	A1