







RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB WELDING DRAWING

Specification

Operating Life	200,000
Contact rating	50mA@12V DC.
Insulation resistance	100MΩ min.
Contact resistance	100mΩ max. initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.25±0.15mm
Storage Temperature	- 30° C to 80° C

Mechanical

Packaging:
Reel of 1,500 pieces.

Type					Operating Force (gf)		Height mm		Button		Leads Shape (G, J, T)		Ground Pin (0, 1)		Pegs Option (0, 1)		X. ± 0.50 X. ° ± 2°		UNITS		mm		博众电气 东莞市博众电气有限公司 BOZHONG ELECTRIC Dongguan Bozhong Electrical Co., Ltd	
																							PART NO.	
																							BTS0E004	
																							TITLE:	
																							TACTILE SWITCH 6.2x6.2mm	
																							APPD: ROGER	
																							CHKD: ROC	
																							DR: BILLY WANG 2020/08/21	
																							DWG NO. :	
																							BTS0E004	
																							SCALE	
																							SHEET	
																							REV.	
																							1/1	
																							1/1	
																							A1	