






RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



P.C.B LAND DIMENSION

Specification


Operating Life	300,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max.initial
Dielectric Strength	250 V AC(1mm)
Travel	0.15±0.1mm
Storage Temperature	- 30° C to 85° C

E	STEM	PA6T	1	Black
D	COVER	Stainless Steel	1	AU
C	DOME	Stainless Steel	1	Plated Ag
B	HOUSING	LCP	1	White
A	PIN	PHOSPHOR BRONZE	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

Mechanical

PN	Operating Force(gf)	Height mm
BTS4T0342AJ00	220±50	2.6
BTS4T0341AJ00	160±50	2.6

Packaging:
Reel of 3,000 pieces.

X. ±0.50	X.° ±2°	UNITS mm	东莞市博众电气有限公司 Dongguan Bozhong Electrical Co., Ltd			
.X ±0.30	.X° ±1°					
.XX ±0.10	.XX° ±0.5°	MAT'L	PART NO. BTS4T034	TITLE: TACTILE SWITCH 微		
.XXX ±0.05						
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DGBZ TECHNOLOGY CO.,LTD		FINISH	APPD: ROGER	DWG NO. : BTS4T034		
		Q' TY	CHKD: ROC			
			DR: BILLY WANG 2020/08/21			