








Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS
 Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C
 Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



P = With Post



默认 = W/O Post

Ordering Information

No. of Rows	No. of Pins	Type	Length (mm)	Contact Plating	R-Rod	Post
1=Single Row	2=40Pin	2=8P		G0:Gold Flash		
2=Dual Row		W=8P		G1:1u" Gold	+Cap	(80%~90%)
		S=8P		G2:3u" Gold		
		VS=8P		G3:5u" Gold		
				G4:10u" Gold		
				G5:15u" Gold		
				G6:30u" Gold		
				S0:Gold Flash/Tin		
				S1:Tin		

GENERAL TOLERANCE			制图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DRAWING				
			审核				
			CHECK				
			批准				
			APPROVAL				
			比例				
			SCALE				
			投影				
			Projection				
序号	变更内容	日期	材料	产品名称	2.00mm 薄等 贴片 偏等+差 (公差4.3)	版本	A
No.	MODIFY CONTENT	MODIFY DATE	MATERIAL	产品料号	PM200-2-N-S-4.3-G0-R	REV.	
				PART NO.		单位	mm
						页次	1/1
						SHEET	