




接触电阻: $\leq 20\text{M}\Omega$
 绝缘电阻: $\geq 1000\text{M}\Omega$
 插拔力: $\geq 0.05\text{kg/P}$, $\leq 0.1\text{kg/P}$
 额定电流: 1A/针
 环境温度: $-55^{\circ} \sim 105^{\circ}$
 焊接温度时间: $\leq 235^{\circ}$, $\leq 3\text{s}$
 触点材质: 磷青铜, (连带)镀镍 $\geq 130\mu$
 绝缘座: PBT
 耐压: 1000VAC60s,
 无击穿. 闪络. 飞弧
 盐雾测试: 24小时不生锈
 沉降盐雾浓度: $(5 \pm 1)\% \text{NaCl (m/m)}$
 试验箱温度: $(35 \pm 2)^{\circ} \text{C}$

24P. 28P. 32P=1.70 其它无筋



8P-PCB LAYOUT

规格	A	B	C	D	E
6	5.08 ^{+0.10} _{-0.10}	7.62 ^{+0.10} _{-0.10}	8.20 ^{+0.20} _{-0.20}	7.62 ^{+0.30} _{-0.30}	10.04 ^{+0.10} _{-0.05}
8	7.62 ^{+0.10} _{-0.10}	10.16 ^{+0.10} _{-0.10}			
14	15.24 ^{+0.10} _{-0.10}	17.78 ^{+0.10} _{-0.10}			
16	17.78 ^{+0.10} _{-0.10}	20.32 ^{+0.10} _{-0.10}			
18	20.32 ^{+0.10} _{-0.10}	22.86 ^{+0.10} _{-0.10}			
20	22.86 ^{+0.10} _{-0.10}	25.40 ^{+0.10} _{-0.10}			
24	27.94 ^{+0.10} _{-0.10}	30.48 ^{+0.10} _{-0.10}			
28	33.02 ^{+0.10} _{-0.10}	35.56 ^{+0.10} _{-0.10}			
32	38.10 ^{+0.10} _{-0.10}	40.64 ^{+0.10} _{-0.10}			
			未生产		

ECN BO.		DESCRIPTION.		DATE.	REV.	SCALE: 1/2	SCALE: 3:1
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				
Mikey	Tom	Jerry	PART NAME	H2541FV-C762-2xXXP	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X.	± 0.25
			MODEL NAME	H2541FV-C762-2xXXP		X.x	± 0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx	± 0.15
						ANGULAIR	± 3
						FILE.NO.	

瀚源