



1.FIGURE AND DIMENSIONS(视图及尺寸)



面板开孔尺寸

Main technical indicators(主要技术指标)	
1.Mating (插拔次数)	500
2.Working Temperature (温度)	-55~+150 ℃
3. IP Rating (防护级别)	IP 44
4.Diameter of socket end(插合端直径)	Ø0.6
5. Testing Voltage (测试电压)	100V
7.Rated Current (额定电流)	2A
8.Shell material (壳体材质)	Zinc alloy nickel plated/锌合金镀亚镍
9.Pin Material(插针材料)	Copper alloy gold plating(铜合金镀金)

Sum up(总结)	
Series(系列)	XKB10
Shell style/model (外壳样式/型号)	7R:Fixed receptacle, panel mount type/直式插头，直通型
Button (按键)	5 button(5个按键)
Termination type (终止类型)	Female solder(母焊锡)
Line diameter awg(线材直径)	22-30AWG
Cable diameterØ (电缆直径)	-
Match plug(匹配插头)	XKB10A. 7P. 6A

版本						TITLE		DRAWING NO.		REV.	
REVA4						XKB10A. 7R插座6芯正装		XKB10A-7R-6L		A0	
REVA3											
REVA2								UNIT		mm	
REVA1								SCALE		Free	
DRAW			DATE			PART NO.		SHEET		10F N	
CHECK			DATE			USE					
APPR' D			DATE								
						XKB INDUSTRIAL PRECISION CO., LIMITED					