





1. FIGURE AND DIMENSIONS (视图及尺寸)




面板开孔尺寸



PCB板开孔尺寸
A-A (比例: 1: 1)

Main technical indicators (主要技术指标)	
1. Mating (插拔次数)	1000
2. Working Temperature (温度)	-55~+150 ℃
3. IP Rating (防护级别)	IP 44
4. Diameter of socket end (插合端直径)	Ø0.6
5. Testing Voltage (测试电压)	100V
7. Rated Current (额定电流)	2A
8. Shell material (壳体材质)	Zinc alloy nickel plated/锌合金镀亚镍
9. Pin Material (插针材料)	Copper alloy gold plating(铜合金镀金)

Sum up(总结)	
Series(系列)	XKB10
Shell style/model (外壳 样式/型号)	10R:Fixed receptacle, panel mount type/固定式插座, 面板安 装型
Button (按键)	5 button(5个按键)
Termination type (终止类型)	Male headers(公板接)
Line diameter awg(线材直 径)	-
Cable diameterΦ (电缆直径)	-
Match plug(匹配插头)	XKB10A. 10P. 12L

版本				TITLE XKB10A. 10R插座12芯 倒装	DRAWING NO.		REV.	
REVA4					XKB10A-10R-12AN		A0	
REVA3					UNIT	mm		
REVA2					SCALE	Free		
REVA1				SHEET	1OF N			
DRAW		DATE		PART NO.				
CHECK		DATE			USE			
APPR' D		DATE				XKB INDUSTRIAL PRECISION CO., LIMITED		