




1. FIGURE AND DIMENSIONS(视图及尺寸)




面板开孔尺寸



PCB板开孔尺寸
A-A(比例：1：1)

Main technical indicators(主要技术指标)	
1.Mating (插拔次数)	1000
2.Working Temperature (温度)	-55~+150 ℃
3. IP Rating (防护级别)	IP 44
4.Diameter of socket end(插合端直径)	φ0.6
5. Testing Voltage (测试电压)	100V
7.Rated Current (额定电流)	2A
8.Shell material (壳体材质)	Zinc alloy nickel plated/锌合金镀亚镍
9.Pin Material(插针材料)	Copper alloy gold plating(铜合金镀金)

Sum up(总结)	
Series(系列)	XKB10
Shell style/model (外壳样式/型号)	10R:Fixed receptacle, panel mount type/固定式插座，面板安装型
Button (按键)	5 button(5个按键)
Termination type (终止类型)	Motherboard headers(motherboard 接)
Line diameter awg(线材直径)	-
Cable diameterφ (电缆直径)	-
Match plug(匹配插头)	XKB10A. 10P. 12A

版本						TITLE		DRAWING NO.		REV.	
REVA4						XKB10A. 10R插座12芯 正装		XKB10A-10R-12LN		A0	
REVA3								UNIT		mm	
REVA2								SCALE		Free	
REVA1								SHEET		10F N	
DRAW			DATE			PART NO.					
CHECK			DATE			USE					
APPR' D			DATE			XKB INDUSTRIAL PRECISION CO., LIMITED					