


1. FIGURE AND DIMENSIONS (视图及尺寸)



Main technical indicators (主要技术指标)	
1. Mating (插拔次数)	1000
2. Working Temperature (温度)	-55~+150 °C
3. IP Rating (防护级别)	IP 44
4. Diameter of socket end (插合端直径)	$\phi 0.6$
5. Testing Voltage (测试电压)	100V
7. Rated Current (额定电流)	2A
8. Shell material (壳体材质)	Zinc alloy nickel plated/锌合金镀亚镍
9. Pin Material (插针材料)	Copper alloy gold plating (铜合金镀金)



面板开孔尺寸

PCB板开孔尺寸
A-A (比例: 1: 1)

Sum up (总结)	
Series (系列)	KKB10
Shell style/model (外壳样式/型号)	10R: Fixed receptacle, panel mount type/固定式插座, 面板安装型
Button (按键)	5 button (5个按键)
Termination type (终止类型)	Male headers (公板接)
Line diameter awg (线材直径)	-
Cable diameter ϕ (电缆直径)	-
Match plug (匹配插头)	KKB10A-10P-10L

版本			TITLE	DRAWING NO.	REV.		
REVA4			XKB10A-10R插座10芯 倒装	XKB10A-10R-10AN	A0		
REVA3							
REVA2							
REVA1							
DRAW		DATE	PART NO.	UNIT	mm		
CHECK		DATE				SCALE	Free
APPR'D		DATE					
USE			XKB INDUSTRIAL PRECISION CO., LIMITED				