





1. FIGURE AND DIMENSIONS(视图及尺寸)




PCB板开孔尺寸
A-A(比例: 1: 1)



面板开孔尺寸

Main technical indicators(主要技术指标)	
1.Mating (插拔次数)	500
2.Working Temperature (温度)	-55~+150 ℃
3.IP Rating (防护级别)	IP 44
4.Diameter of socket end(插端直径)	∅0.6
5.Testing Voltage (测试电压)	150V
7.Rated Current (额定电流)	2A
8.Shell material (壳体材质)	Zinc alloy nickel plated/锌合金镀亚镍
9.Pin Material(插针材料)	Copper alloy gold plating(铜合金镀金)

Sum up(总结)	
Series(系列)	XKB10
Shell style/model (外壳样式/型号)	7R:Fixed receptacle, panel mount type/直式插头，直通型
Button (按键)	5 button(5个按键)
Termination type (终止类型)	Motherboard headers(motherboard 接)
Line diameter awg(线材直径)	-
Cable diameter∅ (电缆直径)	-
Match plug(匹配插头)	XKB10A. 7P. 5A

版本					TITLE XKB10A. 7R插座5芯正装 PART NO.	DRAWING NO.		REV.	
REVA4						XKB10A-7R-5LN		A0	
REVA3						UNITmm SCALEFree SHEET10F N			
REVA2									
REVA1									
DRAW			DATE		USE	XKB INDUSTRIAL PRECISION CO., LIMITED			
CHECK			DATE						
APPR' D			DATE						