

Specification Sheet

Part Number: 133-04043



Secures two routings together while keeping them separated, to prevent chafing or heat transfer

Inverted retaining legs and narrow opening prevent inadvertent disengagement

Controlled flex and angled entry promote easy installation

Robust arrowhead design provides low insertion effort yet delivers exceptional retention strength in an 8mm hole

Tube and Pipe Clip with 8mm Fir Tree, 2x 6.5-7.0mm Diameter, PA66HIRHS, Black, 2000/ctn

Article Number	133-04043
----------------	-----------

Type	PC6.5x2FT8
------	------------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	This clip features a modular design that can be used individually or lined together to secure multiple pipes or hoses.
---------------------	--

Short Description	Tube and Pipe Clip with 8mm Fir Tree, 2x 6.5-7.0mm Diameter, PA66HIRHS, Black, 2000/ctn
-------------------	---

Global Part Name	PC6.5x2FT8-PA66HIRHS-BK
------------------	-------------------------

Fixation Method	Fir Tree
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.22
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	5.5
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)