





MSK12C02GX- X

Color : B:Black: W:White

H(mm) : 15:1.5 ,20:2.0 ,25: 2.5



安装参考图

额定电负荷:DC12V 0.1A  
绝缘电阻: > 100MΩ  
对压强度: AG250V(50Hz)1min  
环境温度: -25' A +70C  
相对湿度: (40 ) <95%  
接触电阻: <50MΩ  
动作力: 160gf+50gf  
耐高温: 260°

|          |         |              |                |                        |                                       |            |       |            |     |
|----------|---------|--------------|----------------|------------------------|---------------------------------------|------------|-------|------------|-----|
|          |         | new          |                | 2015/5/3               |                                       | A          |       | 瀚源         |     |
| ECN BO.  |         | DESCRIPTION. |                | DATE.                  |                                       | REV.       |       |            |     |
| DESIGNED | CHECKED | APPROVAL     | DRAWING NUMBER |                        |                                       | SCALT: 1/2 |       | SCALE: 3:1 |     |
| Mikey    | Tom     | Jerry        | PART NAME      | MSK12C0G2X-X           | UNLESS OTHERWISE SPECIFIED,TOLERANCE: |            | X.    | ±0.25      |     |
|          |         |              | MODEL NAME     | MSK12C0G2X-X           |                                       |            | X.x   | ±0.20      |     |
|          |         |              | 3RD ANGLE PROJ | HanElectricity Co.,LTD |                                       | X.xx       | ±0.15 | ANGULAR    | ±3° |