




SCHEMATIC



RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100MΩ MAX
TRAVEL	2MM
OPERATING FORCE	250±100gf
OPERATING LIFE	10000



L(MM)
2~10

										MODEL TYPE: SLIDE SWITCH					
										PART NO.: SS13F06L					
										DWG NO.:					
XKB INDUSTRIAL PRECISION CO., LIMITED										WEIGHT	SHEET 1/1	REVISION A0			
										DSND			SCALE: N/A		
										DWN					
										VIEW: 					
										CHKD			UNIT: mm/in		
										APPD			SIZE: A4		
										ANGLAR		±5°			
										L ≤ 4		±0.2			
ΔX															
										4<L ≤ 16		±0.3			
ΔX															
										16<L ≤ 63		±0.4			
ΔX															
										L > 63		±0.5			
MARK										DESCRIPTION		DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
										REVISIONS					
										www.hellokko.com		www.hellokko.cn		www.xk-dg.cn	