



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:NYLON RESIN UL94V-0

b.CONTACT:PHOSPHOR BRONZE

(SURFACE PLATING: Au1u")

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTRIC VOLTAGE: 500V AC ONE SEC LEVEL

b.OPERATING TEMPERATURE: -10°C~ +100°C

ORDERING INFORMATION

BH-18650-B***008

电池盒

电池型号

SMT 180° TYPE

PLATING:

A-Au1U"

J-Ni100U"~120U"

K-Sn100U"~120U"

MATERIAL:

1A-PBT BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK

4A-LCP WHITE

4B-LCP BLACK


5A-PA9T BLACK

5B-NYLON RESIN

工程部

2022-03-26

H. WANG



PCB Layout Diagram

Bottom View

2	TERMINAL	1	PHOSPHOR BRONZE, T=0.35MM	Au-Plating
1	HOUSING	1	NYLON RESIN	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com					
DECIMALS:	ANGLES:	DSND	YangFeng	DATE	2022-03-26	TITLE:	
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2022-03-26	电池盒BH-18650-1J Au SMT带柱	
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2022-03-26	PART NO.:	
X.XX :±0.20		WEIGHT:		SCALE:	SIZE: A4	VIEW:	BH-18650-B5BA008
X.XXX :±0.10		SHEET 1 OF 1		UNIT: mm	REV.: A/0	OBJECT: MY	DRAW NO.:WD-CP-0200