





Color : B:Black: W:White

H(mm) : 10:1.0,15:1.5 ,20:2.0 ,30: 3.0

额定电压:DC12V 0.1A
绝缘电阻: > 100MΩ
对压强度: AG250V(50Hz)1min
环境湿度: -25℃ ~ +70℃
相对湿度: (40 ~ 95%)
接触电阻: <50MΩ
动作力: 170gf+20gf
耐高湿: 260℃

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	MSS22C02KGX-X	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.	±0.25	
			MODEL NAME	MSS22C02KGX-X			X.x	±0.20	
			3RD ANGLE PROJ	HanElectricity Co.,LTD					ANGULAR
				FILE.NO.					