




SCHMATIC (SHORTING)

SK12D07VG X  
 H(mm) : 2~12



P.C.B LAYOUT  
 BOTTOM VIEW

注：“\*”表示关键尺寸（3个）。

| NO. | PARTS        | MATERIALS      | Q'TY | FINISH                   |
|-----|--------------|----------------|------|--------------------------|
| 6   | SPRING PLATE | PBS STRIP      | 1    | NATURAL                  |
| 5   | CONTACT CLIP | PBS C5210R-EH  | 1    | Ag PLATED                |
| 4   | TERMINAL     | BRASS STRIP    | 3    | Ag PLATED OVER Ni PLATED |
| 3   | BASE         | PHENOLIC RESIN | 1    | NATURAL                  |
| 2   | KNOB         | POM            | 1    | BLACK                    |
| 1   | FRAME        | STEEL STRIP    | 1    | Ni PLATED                |

| ECN BO.  |         | DESCRIPTION. |                | DATE.                  | REV.   | SCALE: 1/2 | SCALE: 3:1 |
|----------|---------|--------------|----------------|------------------------|--|------------|------------|
| DESIGNED | CHECKED | APPROVAL     | DRAWING NUMBER | 2015/5/3               | A  |            |            |
| Mikey    | Tom     | Jerry        | PART NAME      | SK12D07VGX             |  |            |            |
|          |         |              | MODEL NAME     | SK12D07VGX             | UNLESS OTHERWISE SPECIFIED, TOLERANCE:             |            |            |
|          |         |              | 3RD ANGLE PROJ | HanElectricity Co.,LTD | X. ±0.25<br>X.x ±0.20<br>X.xx ±0.15<br>ANGULAIR ±3 |            |            |
|          |         |              |                |                        | FILE.NO.   |            |            |

瀚源