




SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: 250 $\pm$ 80gf
- 6.Travel:0.25 $\pm$ 0.1mm.
- 7.life test: 10,000 cycles.
- 8.Operation temperature range:-25 $^{\circ}\text{C}$ ~85 $^{\circ}\text{C}$.
- 9.Sign"* "is importance dimension.



CIRCUIT DIAGRAM



P . C . B LAYOUT

H=7.5mm

NO.	PART	NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		A1	2023.2.17	更新图纸	WM	BY	APPD
						<1.5: $\pm 0.1\text{mm}$ >1.5~5.0: $\pm 0.25\text{mm}$ >5.0: $\pm 0.3\text{mm}$	ANGULAR $\pm 1^{\circ}$						
1	TERMINAL		BRASS	1	Ag-PLATED			NO	DATE	REVISIONS			
2	CASE		PA9T	1	BLACK	TITLE: TACT SWITCH			UNIT : MM	ROHS COMPLIANT	DWN		
3	CONTACT		SUS301	1	Ag-PLATED	MODEL: TC-00104-075E			SCALE: 1:1		CHK'D		
4	COVER		BRASS	1	Sn-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司			APPD				
5	KNOB		PA9T	1	BLACK								
									PRO.AGL:			REV :A1	