





MSK12C02GX- X

Color : B:Black: W:White

H(mm) : 15:1.5 ,20:2.0 ,25: 2.5



安装参考图

额定电负荷:DC12V 0.1A
 绝缘电阻: > 100MΩ
 对压强度: AG250V(50Hz)1min
 环境温度: -25' A +70C
 相对湿度: (40) <95%
 接触电阻: <50MΩ
 动作力: 160gf+50gf
 耐高温: 260°

		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	MSK12C0G2X-X	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	MSK12C0G2X-X			X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx ±0.15	
							ANGULAR	±3°	
							FILE.NO.		