







- 1、工作电压 Working Voltage: 12V DC;
- 2、工作电流 Working Current: 0.1A;
- 3、接触电阻 Contact Resistance: $\leq 100\text{m}\Omega$;
- 4、绝缘电阻 Insulation Resistance: $\geq 100\text{M}\Omega$;
- 5、动作力 Press Force: $200 \pm 30\text{gf}$;
- 6、寿命 Life: $>10,000$ 次。

印制线路板

Recommended P.C.B layout



MST23D19GX- X

Color : B:Black: W:White

H(mm) : 20:2.0,30: 3.0,40: 4.0

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	MST23D19GX-X	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.	±0.25	
			MODEL NAME	MST23D19GX-X			X.x	±0.20	
			3RD ANGLE PROJ	HanElectricity Co.,LTD					X.xx
							ANGULAR	±3°	
							FILE.NO.		