



Recommended PCB
Layout ±0.05

Specifications:

规格:

- Voltage rating: 30V AC/DC
- 额定电压: 30V AC/DC
- Current rating: 0.3A AC/DC
- 额定电流: 0.3A AC/DC
- Withstanding voltage: 100V AC/minute
- 耐受电压: 100V AC/分钟
- Temperature range: -35°C~+85°C
- 温度范围: -35°C~+85°C
- Insulation resistance: 50MΩ min
- 绝缘电阻: 50MΩ Min
- Contact resistance: 90mΩ Max
- 接触电阻: 90mΩ Max

X0408 F V S - XX X - LP V01

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- Series No
- Category: F-Female
- Welding Board Angle: V-Stright 180°
- Welding Way: S-SMT
- Row No. Pin No: XX-10~100P
- Height: A=1.5 ; B=2.0 ; C=2.5 ; D=3.0 ; E=3.5 ; F=4.0mm
- Material: LP-LCP UL94V-0 Black
- Plating: V01-Gold Flash

Poles	Dimensions(mm)		
	A	B	C
10	4.60	1.60	1.00
12	5.00	2.00	
20	6.60	3.60	
24	7.40	4.40	1.20
30	8.60	5.60	1.50
34	9.40	6.40	2.30
40	10.60	7.60	
50	12.60	9.60	3.20
60	14.60	11.60	
70	16.60	13.60	
80	18.60	15.60	
90	20.60	17.60	
100	22.60	19.60	

HEIGHT		
H(Socket)	H(Plug)	Mating height
1.45	1.14	A=1.5
1.95		B=2.0
2.40		C=2.5
2.90		D=3.0
3.40		E=3.5
3.90		F=4.0

X0408FVS-XXX-LPV01	LCP	Phosphor Bronze	X0408W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

DSND		SCALE: N/A	MODEL TYPE: 0.4mm BTB Connector
DWN		VIEW:	PART NO.: X0408FVS-XXX-LPV01
CHKD		UNIT: mm/in	DWG NO.: X-X0408FVS-XXX-LPV01
APPD		SIZE: A4	



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

广东星坤科技股份有限公司

DATE	日期
MARK	文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

ANGLAR ±5°
L ≤ 4 ±0.2
4 < L ≤ 16 ±0.3
16 < L ≤ 63 ±0.4
L > 63 ±0.5