





REV.	ECN.NO.	MODIFY.CONTENT
A		







A—A



B—B

性能:
 额定电流: 0.5A
 额定电压: 50V
 耐电压: 500V
 接触电阻: $\leq 20m\Omega$
 绝缘电阻: $800M\Omega$
 工作温度: $-20^{\circ}C \sim +85^{\circ}C$

塑件(材质): LCP, UL94V-0
 锁扣(材质): LCP, UL94V-0
 插簧(材质): 磷青铜, 镀雾锡
 焊片(材质): 磷青铜, 镀雾锡



孔位	A	B	C	D
2	1	3.2	7.2	9
3	2	4.2	8.2	10
4	3	5.2	9.2	11
5	4	6.2	10.2	12
6	5	7.2	11.2	13
7	6	8.2	12.2	14
8	7	9.2	13.2	15
9	8	10.2	14.2	16
10	9	11.2	15.2	17
11	10	12.2	16.2	18
12	11	13.2	17.2	19
13	12	14.2	18.2	20
14	13	15.2	19.2	21
15	14	16.2	20.2	22
16	15	17.2	21.2	23
17	16	18.2	22.2	24
18	17	19.2	23.2	25
19	18	20.2	24.2	26
20	19	21.2	25.2	27
21	20	22.2	26.2	28
22	21	23.2	27.2	29
23	22	24.2	28.2	30
24	23	25.2	29.2	31
25	24	26.2	30.2	32
26	25	27.2	31.2	33
27	26	28.2	32.2	34
28	27	29.2	33.2	35
29	28	30.2	34.2	36
30	29	31.2	35.2	37

GENERAL TOLERANCE		DWG.NO.	1.0K-GL-nPB	PART.NO.	XDFC-10GL-**-P	DRAWN	lixiaoli 12/25'07	UNIT	mm	SCALE	NO SCALE
x. ± 0.30	x. $^{\circ}\pm 5^{\circ}$	REV.	A	TITLE	1.0mm FPC Connectors(L type)	CHECKED		深圳市连欣科技有限公司			
.x ± 0.25	.x $^{\circ}\pm 2^{\circ}$	SIZE		SHEET	1 / 1	APPROVED					
.xx ± 0.20	.xx $^{\circ}\pm 1^{\circ}$	A4									