ROHS Compliant

| MAPX | MODIFICATION | DATE | DRAW | APPROVE |
|---|---|---|---|---|
| | | | | |






3D View




NOTES:
1:MATERIAL
1-1: SUS-301 THICKNE=0.08MM
2:SPECIFICATIONS
2-1: RATED CURRENT: 1.0A
2-2: VOLTAGE RATING: 1.5V
2-3: CONTACT RESISTANCE: 80mΩ/MAX
2-4: WELDING THRUST: ≥3KG
2-5: OPERATING TEMPERATURE: -40°C~+85°C
3:DURABILITY: 1500 CYCLES
4:SALT SPRAY TIME: 24H
5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN
6:REQUIREMENTS
6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE
6-2:ROHS、REACH、HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS




RECOMMENDED PCB LAYOUT

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)




METAL MASK T=0.08

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)







(For Reference Only)
Stated At Compression

| | | | |
|---|---|---|---|
| MANUFACTURE DWG | | 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co,Ltd | |
| UNLESS OTHERWISE SPECIFED TOLERANCES | | TITLE: 天线弹片 L2.10*W1.00*H1.35 | |
| | | PAR | ASP-D1301-B01 |
| | | DWN | |
| | | CHKD | |
| | | APVD | |
| DECIMALS: | ANGLES: | SCALE N:A | UNIT:MM |
| X. ±0.30 | X. ° ±0.20 | | |
| .X ±0.20 | .X ° ±0.10 | | |
| . XX ±0.15 | .XX ° ±0.5 | CUSTOMER COPY | SIZE:A4 SHEET:1F1 REV:A |