

Specifications:

规格:

Voltage rating:300V AC/DC

额定电压: 300V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-55℃--+125℃

温度范围: -55℃--+125℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:40mΩ Max

接触电阻: 40mΩ Max

X0811 F V S- XX X S-LP V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.Series No

2.Category:Female

3.Welding Board Angle:V-Straight 180°

4.Welding Way:S-SMT




5.Row No-Pin No:XX-10Pin-200Pin

6.Height:A=5.0; B=7.0; C=9.0mm

7.speclal No:S-With positioning Column

8.Material:LP-LCP UL94V-0

9.Plating: V01-Gold Flash







MATED HEIGHT				
Female	Male			
	2.00	5.00	8.00	9.00
5.00	7.00	10.00	13.00	14.00
7.00	9.00	12.00	15.00	16.00
9.00	11.00	14.00	17.00	18.00

HEIGHT	H
5.00	5.10
7.00	7.00
9.00	9.00

Poles	A	B	C	D
10	10.00	8.32	3.32	6.80
20	14.00	12.32	7.20	10.80
22	14.80	13.12	8.00	11.60
24	15.60	13.92	8.88	12.40
26	16.40	14.72	9.60	13.20
30	18.00	16.32	11.20	14.80
40	22.00	20.32	15.20	18.80
50	26.00	24.32	19.20	22.80
60	30.00	28.32	23.20	26.80
80	38.00	36.32	31.20	34.80
100	46.00	44.32	39.20	42.80
120	54.00	52.32	47.20	50.80
140	62.00	60.32	55.20	58.80
150	66.00	64.32	59.20	62.80
200	86.00	84.32	79.20	82.80

X0811FVS-XXXS-LPV01	LCP	Phosphor Bronze	X0811W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

DSND		SCALE: N/A	MODEL TYPE: 0.80mm BTB Style Connector		
DWN		VIEW: 	PART NO.: X0811FVS-XXXS-LPV01		
CHKD		UNIT: mm/in	DWG NO.: X-X0811FVS-XXXS-LPV01		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0



Recommended PCB Layout

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED