


SCHEMATIC (SHORTING)

SK14D07VG X

H(mm) : 2~12



**P.C.B LAYOUT
BOTTOM VIEW**

注：“*”表示关键尺寸(5个)。

NO.	PARTS	MATERIALS	Q'TY	FINISH
6	SPRING PLATE	PBS STRIP	1	NATURAL
5	CONTACT CLIP	PBS C5210R-EH	1	Au CLAD
4	TERMINAL	BRASS STRIP	6	Ag PLATED OVER Ni PLATED
3	BASE	PHENOLIC RESIN	1	NATURAL
2	KNOB	POM	1	BLACK
1	FRAME	STEEL STRIP	1	Ni PLATED

DESIGNED		CHECKED		APPROVAL		DRAWING NUMBER		SCALE: 1/2		SCALE: 3:1	
Mikey		Tom		Jerry		PART NAME		SK14D07VGX		UNLESS OTHERWISE SPECIFIED, TOLERANCE:	
						MODEL NAME		SK14D07VGX		X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAIR ±3	
						3RD ANGLE PROJ		HanElectricity Co.,LTD		FILE.NO.	

瀚源