



Recommended PCB  
Layout ±0.05

Specifications:

规格:  
Voltage rating:30V AC/DC  
额定电压: 30V AC/DC  
Current rating:0.3A AC/DC  
额定电流: 0.3A AC/DC  
Withstanding voltage:100V AC/minute  
耐受电压: 100V AC/分钟  
Temperature range:-35°C~+85°C  
温度范围: -35°C~+85°C  
Insulation resistance:50MΩ min  
绝缘电阻: 50MΩ Min  
Contact resistance:90mΩ Max  
接触电阻: 90mΩ Max

X0408 W V S - XX X - LP V01  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-10~100P
- 6.Height:A=1.14mm
- 7.Material:LP-LCP UL94V-0 Black
- 8.Plating:V01-Gold Flash

Poles	Dimensions(mm)		
	A	B	C
10	3.52	1.60	1.00
12	3.92	2.00	
20	5.52	3.60	
24	6.32	4.40	1.20
30	7.52	5.60	1.50
34	8.32	6.40	2.30
40	9.52	7.60	3.20
44	10.32	8.40	
50	11.52	9.60	
60	13.52	11.60	
70	15.52	13.60	
80	17.52	15.60	
90	19.52	17.60	
100	21.52	19.60	

X0408WVS-XXX-LPV01	LCP	Phosphor Bronze	X0407F
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 0.4mm BTB Connector
DWN	VIEW:	PART NO.: X0408WVS-XXX-LPV01
CHKD	UNIT: mm/in	DWG NO.: X-X0408WVS-XXX-LPV01
APPD	SIZE: A4	

					ANGULAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0