







A-A



B-B

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:800V AC/minute

耐受电压: 800V AC/分钟

Temperature range:-40℃~+85℃

温度范围: -40℃~+85℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2011	T	M	- P	SN	- A
①	②	③	④	⑤	⑥

1.Series No

2.Category:T-Terminal

3.Category:M-Male Terminal

4.Material:P-Phosphor Bronze

5.Plating:SN-Tin Plating

6.TYPE:A Type

X2011TM-PSN-A	Phosphor Bronze	AWG#30~24	X2011HF
PART NO	Material	Wire Range	Suitable XKB Housing

广东星坤科技股份有限公司	
DATE	日期
DESIGN	设计
CHKD	审核
APPD	批准
MARK	文件工程章

DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
				L≤ 4	±0.2
				4<L≤ 16	±0.3
				16<L≤ 63	±0.4
				L> 63	±0.5

XKLB

DSND	SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connector
DWN	VIEW:	PART NO.: X2011TM-PSN-A
CHKD	UNIT: mm/in	DWG NO.: X2011TM-PSN-A
APPD	SIZE: A4	

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0